



**Inch table**

Dimensions in: inches - *millimeters*

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Thread	$d_3$	$h_1$	$h_2$	$t$
1.13 28.7	1/4 x 20	0.50 12.7	0.75 19.1	0.13 3.3	0.38 9.7

**Specification**

- Wing body  
Phenolic plastic  
- Glass filled  
- Temperature resistant up to 300 °F (149 °C)  
- Black, shiny finish
- Tapped insert  
Brass
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

**Information**

Due to its low height the FTK wing nut offers a comfortable grip for quick two finger clamping applications.

see also...

- *Wing Nuts FKS (Nylon Plastic)* → [www.jwwinco.com](http://www.jwwinco.com)

**On request**

- Additional thread sizes

How to order <sup>1</sup> <sup>2</sup> <b>FTK-1.13-1/4X20</b>	1	Handle diameter $d_1$
	2	Thread $d_2$