



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub> Thread	Length l									b	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>
		GP			GPX									
34 1.34	M 6	10 0.39	15 0.59	20 0.79	25 0.98	-	-	-	20 0.79	30 1.18	14 0.55	18 0.71	4 0.16	.3 .01
34 1.34	M 8	10 0.39	15 0.59	20 0.79	25 0.98	-	-	-	-	-	14 0.55	18 0.71	4 0.16	.3 .01
47 1.85	M 6	10 0.39	15 0.59	20 0.79	25 0.98	-	-	-	-	-	17 0.67	20 0.79	4 0.16	.3 .01
47 1.85	M 8	10 0.39	15 0.59	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	-	-	17 0.67	20 0.79	4 0.16	.3 .01

**Specification**

- Wing body  
Nylon plastic  
- Glass filled  
- Temperature resistant up to 230 °F (110 °C)  
- Black, matte finish
- **GP**  
Threaded stud  
Steel, zinc plated
- **GPX**  
Threaded stud  
Stainless steel AISI 304
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**On request**

- For certain minimum quantities, custom colors or special studs

**Information**

GP and GPX wing screws offer a comfortable two finger grip and expand the range of clamping applications.

How to order (Steel threaded stud)	1 Handle diameter d <sub>1</sub>
<b>GP-47-M6-20</b>	2 Thread d <sub>2</sub>
	3 Length l
How to order (Stainless steel threaded stud)	1 Handle diameter d <sub>1</sub>
<b>GPX-34-M6-30</b>	2 Thread d <sub>2</sub>
	3 Length l

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4