



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	Length l									b	h ₁	h ₂	h ₃
		GP			GPX									
34 1.34	M 6	10 0.39	15 0.59	20 0.79	25 0.98	-	-	-	20 0.79	30 1.18	14 0.55	18 0.71	4 0.16	.3 .01
34 1.34	M 8	10 0.39	15 0.59	20 0.79	25 0.98	-	-	-	-	-	14 0.55	18 0.71	4 0.16	.3 .01
47 1.85	M 6	10 0.39	15 0.59	20 0.79	25 0.98	-	-	-	-	-	17 0.67	20 0.79	4 0.16	.3 .01
47 1.85	M 8	10 0.39	15 0.59	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	-	-	17 0.67	20 0.79	4 0.16	.3 .01

Specification

- Wing body
Nylon plastic
- Glass filled
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- **GP**
Threaded stud
Steel, zinc plated
- **GPX**
Threaded stud
Stainless steel AISI 304
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- For certain minimum quantities, custom colors or special studs

Information

GP and GPX wing screws offer a comfortable two finger grip and expand the range of clamping applications.

How to order (Steel threaded stud)	1 Handle diameter d ₁
GP-47-M6-20	2 Thread d ₂
	3 Length l
How to order (Stainless steel threaded stud)	1 Handle diameter d ₁
GPX-34-M6-30	2 Thread d ₂
	3 Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4