



**SS** Stainless Steel

**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	<sup>3</sup> Length l			k
0.63 16.0	10 x 32	1.50 38.1	2.00 50.8	-	0.19 4.8
0.63 16.0	10 x 24	1.50 38.1	2.00 50.8	-	0.19 4.8
0.69 17.5	1/4 x 20	1.50 38.1	2.50 63.5	-	0.22 5.6
0.75 19.1	5/16 x 18	1.75 44.5	2.25 57.2	3.00 76.2	0.25 6.4
0.88 22.4	3/8 x 16	2.00 50.8	2.50 63.5	3.00 76.2	0.31 7.9
1.00 25.4	1/2 x 13	3.00 76.2	-	-	0.38 9.7

**Specification**

- Steel 12L14
- Blackened finish
- Not hardened

<sup>4</sup>

**ST**

- Stainless steel AISI 303
- *Stainless Steel Characteristics* → page 2143

**NI**

• [RoHS compliant](#)

**Information**

KHS knurled thumb screws are used for jig and fixture work.

see also...

- *Knurled Thumb Screws DPHS (with Dog Point)* → page 709

**How to order**

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup>  
**KHS-0.63-10X32-1.50-ST**

<sup>1</sup>	Handle diameter d <sub>1</sub>
<sup>2</sup>	Thread d <sub>2</sub>
<sup>3</sup>	Length l
<sup>4</sup>	Material