



Inch table

Dimensions in: inches - *millimeters*

¹ d_1	² d_2 Thread	d_3	h	t
1.00 25.4	1/4 x 20	0.63 16.0	0.81 20.6	0.50 12.7
1.38 35.1	5/16 x 18	0.75 19.1	0.81 20.6	0.50 12.7
1.88 47.8	5/16 x 18	1.00 25.4	1.00 25.4	0.50 12.7
1.88 47.8	3/8 x 16	1.00 25.4	1.00 25.4	0.50 12.7

Specification

- Knurled nut
Polypropylene plastic
- Temperature resistant up to 150 °F (66 °C)
- Black, matte finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

On request

- Additional thread sizes

Information

More shock proof than their phenolic counterpart, these KKBH knurled nuts provide excellent slip-free clamping and fastening.

How to order ¹ ² KKBH-1.88-3/8X16	1 Handle diameter d_1
	2 Thread d_2