Knurled Screws

Steel or Stainless Steel

JW WINCO® A Ganter Company

Inch



SS Stainless Steel

Inch table

Dimensions in: inches / millimeters

1 d_1	2 d_2	3 Length l		d_3	h	k
0.75 19.1	10 x 24	0.50 12.7	1.00 25.4	0.50 12.7	0.63 16	0.25 6.4
0.75 19.1	1/4 x 20	0.75 19.1	1.25 31.8	0.50 12.7	0.63 16	0.25 6.4
1.00 25.4	1/4 x 20	1.75 44.5	-	0.63 16	0.75 19.1	0.25 6.4
1.00 25.4	5/16 x 18	1.75 44.5	3.00 76.2	0.63 16	0.75 19.1	0.25 6.4
1.50 38.1	5/16 x 18	1.75 44.5	3.00 76.2	0.75 19.1	1.00 25.4	0.31 7.9
1.50 38.1	3/8 x 16	1.75 44.5	3.00 76.2	0.75 19.1	1.00 25.4	0.31 7.9
2.00 50.8	3/8 x 16	1.75 44.5	3.00 76.2	1.00 25.4	1.13 28.7	0.38 9.7
2.00 50.8	1/2 x 13	1.75 44.5	-	1.00 25.4	1.13 28.7	0.38 9.7
2.50 63.5	1/2 x 13	1.75 44.5	3.00 76.2	1.50 38.1	1.50 38.1	0.56 14.2
2.50 63.5	5/8 x 11	1.75 44.5	-	1.50 38.1	1.50 38.1	0.56 14.2

Specification

4	
Stainless steel AISI 303	**NI**
Steel, blackened finish	**ST**

RoHS

On request

- Special stud lengths and stud variations

Knurled screws KRSK are used for applications which require higher durability than plastic or aluminum, yet appearance is essential.

see also...	Page
KRSK Knurled Nuts (with Tapped or Plain Bore)	QVX

Technical Information

Stainless Steel Characteristics	QVX

How to order

1 2 3 4

KRSK-1.50-5/16X18-3.00-NI

1	**Handle diameter d_1**
2	**Thread d_2**
3	**Length l**
4	**Material**

⚠ **WARNING**: Cancer and Reproductive Harm — www.P65Warnings.ca.gov