



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	<sup>3</sup> Length l		d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
30 1.18	M 6	20 0.79	30 1.18	14 0.55	24 0.94	15 0.59	9 0.35
40 1.57	M 8	20 0.79	30 1.18	16 0.63	28 1.10	18 0.71	13 0.51
50 1.97	M 10	25 0.98	30 1.18	18 0.71	32 1.26	20 0.79	16 0.63

**Specification**

- Six-lobed knob  
Nylon plastic
  - Temperature resistant up to 230 °F (110 °C)
  - Glass filled
  - Black, matte finish
- **LBX**  
Tapped insert  
Stainless steel AISI 304
- **LPX**  
Threaded stud  
Stainless steel AISI 304
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**Information**

LBX is an economical but durable six-lobed knob for many applications.

How to order (Tapped insert) <sup>1</sup> <sup>2</sup> <b>LBX-50-M10</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
How to order (Threaded stud) <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>LPX-40-M8-30</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
	3	Length l

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

