



Metric table

Dimensions in: millimeters - inches

| ¹ b | ² d Thread | ³ l ₁ | h ₁ | h ₂ | l ₂ | l ₃ |
|----------------|--------------------------|-----------------------------|----------------|----------------|----------------|----------------|
| 21 0.83 | M 6 | 93.5 3.68 | 36 1.42 | 30 1.18 | 112 4.41 | 15 0.59 |
| 26 1.02 | M 6 | 117 4.61 | 41 1.61 | 34 1.34 | 139 5.47 | 15 0.59 |
| 27 1.06 | M 6 | 132 5.20 | 45 1.77 | 37 1.46 | 156 6.14 | 15 0.59 |
| 28 1.10 | M 6 | 179 7.05 | 50 1.97 | 42 1.65 | 204 8.03 | 15 0.59 |

Specification

- Nylon plastic
 - Black, RAL 9005, matte finish **● SW**
 - Temperature resistant up to 230 °F (110 °C)
- Threaded studs
Steel, zinc plated
- Strength Values → page 2081
- Plastic Characteristics → page 2135
- RoHS compliant

Information

The shape of MFP cabinet “U” handles has good ergonomic features. Because of the style and durability of these handles, they are suitable for most industries.

see also...

- Cabinet “U” Handles MFB → page 112

On request

- Various metric size fasteners and kit packaging

| | |
|--|--------------------------------|
| How to order ¹ ² ³ ⁴ MFP-27-M6-132-SW | 1 Handle width b |
| | 2 Thread d |
| | 3 Length l ₁ |
| | 4 Color |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4