



Metric table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁ Bore		d ₂	d ₃ Set screw	h ₁	h ₂	l ₂	l ₃
35 1.38	B 6	-	25 0.98	M 4	18 0.71	15 0.59	20 0.79	15 0.59
45 1.77	B 8	-	30 1.18	M 4	21.5 0.85	17 0.67	25 0.98	20 0.79
55 2.17	B 6	B 10	35 1.38	M 4	25 0.98	19 0.75	30 1.18	25 0.98

Specification

- Plastic
Duroplast (Phenolic)
- Black, shiny finish
- Temperature resistant up to 300 °F (150 °C)
- Slotted set screw
Steel
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

On request

- Modifications such as inch and metric blind bores

Information

MRI is a standard pointer knob that can be utilized with graduated dials.

see also...

- *Six-Lobed Flanged Control Knobs VBI (Phenolic Plastic)* → www.jwwinco.com

How to order ¹ ² MRI-55-B10	1	Length l ₁
	2	Bore d ₁

