



Metric table

Dimensions in: millimeters - inches

¹ b	² d Thread	³ l ₁	h ₁	h ₂	l ₂	t
30 1.18	M 6	105 4.13	48 1.89	30 1.18	140 5.51	13 0.51
30 1.18	M 6	110 4.33	48 1.89	30 1.18	140 5.51	9 0.35
30 1.18	M 8	117 4.61	48 1.89	30 1.18	140 5.51	15 0.59
30 1.18	M 6	120 4.72	48 1.89	30 1.18	140 5.51	9 0.35
30 1.18	M 8	120 4.72	48 1.89	30 1.18	140 5.51	9 0.35
36 1.42	M 8	132 5.20	56 2.20	36 1.42	160 6.30	15 0.59
36 1.42	M 10	132 5.20	56 2.20	36 1.42	160 6.30	16 0.63

Specification

- Phenolic plastic
 - Black
 - Temperature resistant up to 266 °F (130 °C)
- Tapped Inserts
 - Brass
- [Plastic Characteristics](#) → page 2135
- [RoHS compliant](#)

On request

- For certain minimum quantities, inserts in steel or stainless steel
- Various metric size fasteners and kit packaging

Information

MS cabinet “U” handles have a robust shape and are an excellent choice for applications requiring higher temperature resistance.

see also...

- [Cabinet “U” Handles MT](#) → page 111
- [Cabinet “U” Handles GN 565](#) → page 98

How to order ¹ ² ³ MS-30-M8-120	1 Handle width b
	2 Thread d
	3 Length l ₁

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4