



**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> b	<sup>2</sup> d Thread	<sup>3</sup> l <sub>1</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	t
1.02 26	1/4 x 20	4.13 105	1.46 37	1.14 29	4.76 121	0.35 9
1.02 26	1/4 x 20	4.33 110	1.57 40	1.26 32	5.24 133	0.35 9
1.02 26	5/16 x 18	4.61 117	1.57 40	1.26 32	5.24 133	0.35 9

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> b	<sup>2</sup> d Thread	<sup>3</sup> l <sub>1</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	t	
26 1.02	M 5 M 6	-	105 4.13	37 1.46	29 1.14	121 4.76	9 0.35
26 1.02	M 5 M 6	-	110 4.33	40 1.57	32 1.26	133 5.24	9 0.35
26 1.02	M 5 M 6	M 8	117 4.61	40 1.57	32 1.26	133 5.24	9 0.35

**Specification**

- Nylon plastic
  - Black, RAL 9005, matte finish ● **SW**
  - Glass fiber reinforced
  - Temperature resistant up to 230 °F (110 °C)
- Tapped inserts  
Brass
- Strength Values → page 2081
- Plastic Characteristics → page 2135
- RoHS compliant

**Information**

Ergonomic styling at its best, the MT cabinet “U” handles are a top quality yet economical solution for most any application.

see also...

- Cabinet “U” Handles MFB → page 112
- Cabinet “U” Handles GN 565 → page 98

**On request**

- Additional colors
- Various metric and inch size fasteners and kit packaging

How to order (Inch)	<sup>1</sup> Handle width b
<sup>2</sup> Thread d	<sup>3</sup> Length l <sub>1</sub>
<sup>3</sup> Length l <sub>1</sub>	<sup>4</sup> Color
<b>MT-26-5/16X18-117-SW</b>	

  

How to order (Metric)	<sup>1</sup> Handle width b
<sup>2</sup> Thread d	<sup>3</sup> Length l <sub>1</sub>
<sup>3</sup> Length l <sub>1</sub>	<sup>4</sup> Color
<b>MT-26-M5-110-SW</b>	

1.1 1.2 1.3 1.4 2.1 2.2 2.3 2.4