



Metric table

Dimensions in: millimeters - inches

¹ d_1	² d_2 Bore						d_3	l_1	l_2
23 0.91	B 7	B 8	B 9	B 10	B 12	B 14	18 0.71	60 2.36	55 2.17

Specification

- Plastic
PVC
- Temperature resistant up to 158 °F (70 °C)
- Black
- Molded blind bore
- Push-fit mounting
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

- MVP cylindrical handles offer a comfortable and elastic grip.
- see also...**
- *Tapered Handle MVP-CON* → page QVX

How to order ¹ ² MVP-23-B7	1	Handle diameter d_1
	2	Bore diameter d_2

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

