



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	d ₄	l ₁	l ₂	l ₃	A/F Internal hex
41 1.61	M 8	13 0.51	15 0.59	54 2.13	12 0.47	4
41 1.61	M 10	13 0.51	17 0.67	54 2.13	12 0.47	5
47 1.85	M 8	14 0.55	15 0.59	58 2.28	12 0.47	4
47 1.85	M 10	14 0.55	17 0.67	58 2.28	12 0.47	5
60 2.36	M 8	14 0.55	15 0.59	71 2.80	12 0.47	4
60 2.36	M 10	14 0.55	17 0.67	71 2.80	12 0.47	5

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 266 °F (130 °C)
- Black, shiny finish
- Threaded spindle
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

PB/GE revolving ball knobs can be utilized instead of revolving handles, e.g. with handwheels or crank handles.

see also...

- *Revolving Ball Knobs GN 319.2 (Long Shoulder Type)* → page 42

How to order ¹ ² PB-GE-41-M8	1	Ball diameter d ₁
	2	Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

