



**4 Type**

- C With tapped hole (no insert)
- E With tapped insert

Dimensions in: inches - millimeters

**Inch table**

d <sub>1</sub>		d <sub>2</sub>				d <sub>3</sub> ≈	h	t
Type E	Type C	Thread						
0.75 19.1	-	6 x 32	8 x 32	10 x 24	10 x 32	0.38 9.7	0.70 17.8	0.31 7.9
0.75 19.1	-	1/4 x 20	-	-	-	0.38 9.7	0.70 17.8	0.38 9.7
1.00 25.4	-	10 x 32	-	-	-	0.50 12.7	0.97 24.6	0.31 7.9
1.00 25.4	-	1/4 x 20	1/4 x 28	5/16 x 18	5/16 x 24	0.50 12.7	0.97 24.6	0.44 11.2
1.00 25.4	-	3/8 x 16	3/8 x 24	-	-	0.50 12.7	0.97 24.6	0.50 12.7
1.19 30.2	-	1/4 x 20	5/16 x 18	5/16 x 24	-	0.56 14.2	1.13 28.7	0.44 11.2
1.19 30.2	-	3/8 x 16	3/8 x 24	-	-	0.56 14.2	1.13 28.7	0.50 12.7
1.38 35.1	-	1/4 x 20*	5/16 x 18	5/16 x 24	-	0.63 16.0	1.30 33.0	0.44 11.2
1.38 35.1	-	3/8 x 16	3/8 x 24	7/16 x 20	-	0.63 16.0	1.30 33.0	0.50 12.7
1.38 35.1	-	1/2 x 13	1/2 x 20	-	-	0.63 16.0	1.30 33.0	0.63 16.0
1.50 38.1	-	5/16 x 18	3/8 x 16	-	-	0.63 16.0	1.49 37.8	0.50 12.7
-	1.50 38.1	1/4 x 20	-	-	-	0.63 16.0	1.49 37.8	0.63 16.0
-	1.50 38.1	1/2 x 13	-	-	-	0.63 16.0	1.49 37.8	0.88 22.4
1.63 41.4	-	5/16 x 18	5/16 x 24	-	-	0.69 17.5	1.58 40.1	0.44 11.2
1.63 41.4	-	3/8 x 16	3/8 x 24	7/16 x 20	-	0.69 17.5	1.58 40.1	0.50 12.7
1.63 41.4	-	1/2 x 13	1/2 x 20	-	-	0.69 17.5	1.58 40.1	0.63 16.0
1.88 47.8	-	3/8 x 16	3/8 x 24	-	-	0.75 19.1	1.80 45.7	0.50 12.7
1.88 47.8	-	1/2 x 13	1/2 x 20	-	-	0.75 19.1	1.80 45.7	0.63 16.0
-	1.88 47.8	3/8 x 16	3/8 x 24	-	-	0.75 19.1	1.80 45.7	0.63 16.0
-	1.88 47.8	5/8 x 18	-	-	-	0.75 19.1	1.80 45.7	0.88 22.4

**Specification**

- Plastic **KU**  
Duroplast (Phenolic PF)  
- Temperature resistant up to 300 °F (149 °C)  
- Black, shiny finish
- Plain thread (Type C)  
Molded-in
- Tapped insert (Type E)  
Brass, molded-in
- RoHS compliant

**Information**

PBH ball knobs can be used on machine tools, jigs, fixtures, and a variety of other equipment.

**On request**

- Other colors

<b>How to order</b>	
1	Material
2	Ball diameter d <sub>1</sub>
3	Thread d <sub>2</sub>
4	Type

**PBH-KU-0.75-6X32-E**