



Inch



Inch table

¹ A/F	² d ₂	³ l ₁	l ₂	e	Max. load
0.563 14.3	1/4 x 20	1.00 25.4	0.093 2.4	0.625 15.9	1000 lbf 4448.22 N
0.750 19.1	5/16 x 18	1.50 38.1	0.109 2.8	0.842 21.4	2300 lbf 10230.9 N
0.875 22.2	3/8 x 16	1.50 38.1	0.140 3.6	0.986 25	3750 lbf 16680.83 N
0.875 22.2	3/8 x 16	2.50 63.5	0.140 3.6	0.986 25	3750 lbf 16680.83 N
1.063 27	1/2 x 13	2.50 63.5	0.171 4.3	1.204 30.6	5000 lbf 22241.1 N

Dimensions in: inches / millimeters

Specification

Low carbon steel

- Clear zinc plated
- No articulation

RoHS

Hex leveler bolts SN 949 are ideal for light duty industrial appliances where cost is a primary concern. Common uses are in sheet metal enclosures and appliances.

see also...

	Page
SN 974 Rattle Mounts (Inch Size, with Optional Slot)	QVX
SN 946 Willi Glide Leveling Mounts (Inch Size, with Plastic / Rubber Pad)	QVX

How to order

SN 949-0.563-1/4X20-1.00

- ¹ Across flats
- ² Thread d₂
- ³ Length l₁

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10