



- 4 Type**
- A Without slot
 - S With slot at the top

Inch table

1		2	3			4		Dimensions in: inches - millimeters
d ₁	d ₂ Thread	l ₁	l ₁	l ₁	l ₂	l ₂	Max. load	
1.75 44.5	3/8 x 16	1.25 31.8	1.75 44.5	2.75 69.9	0.50 12.7	0.50 12.7	500 lbf 2224.11 N	

Specification

- Base / stud
Steel
- Clear zinc plated
- Slight articulation
- RoHS compliant

Information

SN 974 rattle mounts are used for light duty applications such as home gaming and vending machines. These low cost levelers also have an optional slot on top for adjusting height with a screwdriver.

see also...

- Hex Leveler Bolts SN 949 → page 1499
- Willi Glide Leveling Mounts SN 946 (with Plastic / Rubber Pad) → page 1498

How to order	1 Base diameter d ₁
1 2 3 4	2 Thread d ₂
SN974-1.75-3/8X16-1.75-S	3 Stud length l ₁
	4 Type