



3 Type
A Without dipstick
B With dipstick

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Fine thread	d ₃	l ₁	l ₂	l ₃
25 0.98	M 14 x 1.5*	-	13 0.51	18 0.71	-
25 0.98	M 18 x 1.5	4 0.16	13 0.51	18 0.71	72 2.83

*Only available in type A

Specification

- Body
Nylon plastic
- Screw-fit
- Red
- Temperature resistant up to 176 °F (80 °C)
- Seal
Synthetic rubber, fluid resistant
- *Plastic Characteristics* → page QVX
- *RoHS compliant*

Information

TA1-2 breather valve caps are provided without a symbol and no dipstick markings.
 Complete with unmounted seal.

see also...

- *Breather Valve Caps TA3-7 (with Pipe Thread)* → page QVX

How to order 1 2 3 TA1-2-25-M14X1.5-A	1 Diameter d ₁
	2 Fine thread d ₂
	3 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10