



**Inch table**

Dimensions in: inches - millimeters

Length l	d <sub>1</sub> Thread		d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	t	
2.25 57.2	1/4 x 20	5/16 x 18	3/8 x 16	0.75 19.1	1.44 36.6	0.69 17.5	0.50 12.7

**Specification**

- Plastic  
Nylon  
- Temperature resistant up to 200 °F (93 °C)  
- Black, matte finish
- Tapped insert  
Brass
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

**On request**

- Additional thread sizes
- Special stud assemblies (glued into place)

**Information**

TBK T-bar knobs are a great choice for pull-action applications due to their ergonomically rounded shape.

<p>How to order</p> <p><b>TBK-2.25-3/8X16</b></p>	1	Handle length l
	2	Thread d <sub>1</sub>