



**Inch table**

Dimensions in: inches - millimeters

Length l	d <sub>1</sub> Thread		Steel	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	t
	Brass						
2.50 63.5	1/4 x 20	5/16 x 18	-	0.75 19.1	1.13 28.7	0.50 12.7	0.50 12.7
3.50 88.9	3/8 x 16	-	-	0.94 23.9	1.13 28.7	0.50 12.7	0.50 12.7
3.50 88.9	-	-	1/2 x 13	0.94 23.9	1.13 28.7	0.30 7.6	0.88 22.4

**Specification**

- Plastic  
Polypropylene
  - Temperature resistant up to 125 °F (52 °C)
  - Black, matte finish
- Tapped insert
  - Brass **MS**
  - Steel, zinc plated **ST**
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

**Information**

The wide surface area of the TH T-bar knobs allow for positive low profile clamping.

**On request**

- Special stud assemblies (glued into place)

How to order	1 Handle length l
TH-2.50-5/16X18-MS	2 Thread d <sub>1</sub>
	3 Material