



Metric table

Dimensions in: millimeters - inches

Length ¹ l	d ² Thread	h ₁	h ₂	b	t
57 2.24	M 6	30 1.18	16 0.63	15 0.59	13 0.51
57 2.24	M 8	30 1.18	16 0.63	15 0.59	15 0.59

Specification

- Plastic
Nylon
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
 - Glass filled
 - Molded-in thread
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Special stud assemblies (glued into place)

Information

The wide surface area of TIR T-bar knobs allow for positive low profile clamping.
Resistant to solvents, oils, grease and other chemical agents.

see also...

- T-Handles (Aluminum) → page 81

How to order ¹ ² TIR-57-M6	1	Handle length l
	2	Thread d

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4