



Metric table

Dimensions in: millimeters - inches

d ₁	d ₂			d ₃	h ₁	h ₂	t	
	M 6	M 8	M 10				V3-B	V3-B-FP
45 1.77	M 6	M 8	M 10	18 0.71	27 1.06	16 0.63	14 0.55	15 0.59
55 2.17	M 8	M 10	M 12	20 0.79	33 1.30	19 0.75	14 0.55	15 0.59

Specification

- Three-lobed knob
Nylon plastic
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

On request

- Stainless steel insert

Information

V3-B and V3-B-FP three-lobed knobs have an aesthetically pleasing shape and provide a comfortable grip.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Three Lobed Knobs V3-B-P (with Steel Threaded Stud)* → page 655

How to order (Blind tapped insert) ¹ ² V3-B-45-M8	1	Handle diameter d ₁
	2	Thread d ₂
How to order (Through tapped insert) ¹ ² V3-B-FP-55-M10	1	Handle diameter d ₁
	2	Thread d ₂