



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂			d ₃	h ₁	h ₂	t
20 0.79	M 4	M 5	M 6	13 0.51	15 0.59	7 0.28	9 0.35
30 1.18	M 5	M 6	-	17 0.67	24 0.94	11 0.43	9 0.35
30 1.18	M 8	-	-	17 0.67	24 0.94	11 0.43	15 0.59
40 1.57	M 6	-	-	21 0.83	28 1.10	12 0.47	13 0.51
40 1.57	M 8	-	-	21 0.83	28 1.10	12 0.47	15 0.59
40 1.57	M 10	-	-	21 0.83	28 1.10	12 0.47	16 0.63
50 1.97	M 8	-	-	25 0.98	33 1.30	13 0.51	15 0.59
50 1.97	M 10	-	-	25 0.98	33 1.30	13 0.51	16 0.63
50 1.97	M 12	-	-	25 0.98	33 1.30	13 0.51	18 0.71

Specification

- Six-lobed knob
Phenolic plastic
 - Temperature resistant up to 300 °F (150 °C)
 - Black, shiny finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

On request

- For certain minimum quantities, stainless steel inserts

Information

The solid design of the VB six-lobed knobs is an excellent choice for food applications or any application where bacteria accumulation is unwanted.

see also...

- *Six-Lobed Knobs VB-FP (with Tapped Through Insert)* → page 591
- *Six-Lobed Knobs VP (with Steel Threaded Stud)* → page 592

How to order ¹ ² VB-20-M5	1	Handle diameter d ₁
	2	Thread d ₂