



Metric table

Dimensions in: millimeters - inches

d₁ Type S	d₂ D9 Bore	d₃	d₄ Set screw	h₁	h₂
20 .79	B 6	30 1.18	M 4	18 .71	15 .59
30 1.18	B 6	40 1.57	M 4	27 1.06	21 .83
40 1.57	B 6	48 1.89	M 4	30 1.18	22 .87
40 1.57	B 8	48 1.89	M 4	30 1.18	24 .94
50 1.97	B 6	56 2.20	M 4	35 1.38	22 .87
50 1.97	B 8	56 2.20	M 4	35 1.38	24 .94
70 2.76	B 6	90 3.54	M 4	50 1.97	30 1.18
70 2.76	B 8	90 3.54	M 4	50 1.97	30 1.18
70 2.76	B 12	90 3.54	M 4	50 1.97	30 1.18

Specification

- Plastic
Duroplast (Phenolic PF)
- Black, shiny finish
- Temperature resistant up to 230 °F (110 °C)
- Flange
Black glass filled nylon plastic, shiny finish
- Insert
Brass, molded-in
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

On request

- Modifications such as inch and metric blind bores

Information

VBI is an excellent quality and very attractive six-lobed control knob.

see also...

- Control Knobs with Pointer EN 5338 → page QVX
- Pointer Knobs MRI (Phenolic Plastic) → page QVX

<p>How to order</p> <p>VBI-20-B6</p>	1	Outside diameter d ₁
	2	Bore d ₂