



**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	t	
						VBZ	VBZ-FP
26 1.02	M 6	20 0.79	7 0.28	16 0.63	6 0.24	9 0.35	8 0.31
26 1.02	M 8	20 0.79	9 0.35	16 0.63	6 0.24	9 0.35	8 0.31

**Specification**

- Knurled nut  
Phenolic plastic  
- Temperature resistant up to 302 °F (150 °C)  
- Black, shiny finish
- Tapped insert  
Brass
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

**Information**

For slip-free fastening and clamping, these VBZ and VBZ-FP knurled nuts are an excellent economical choice.

see also...

- *Knurled Screws VPZ (with Steel Threaded Stud)* → page 690

How to order (Blind tapped insert) <sup>1</sup> <sup>2</sup> <b>VBZ-26-M8</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
How to order (Through tapped insert) <sup>1</sup> <sup>2</sup> <b>VBZ-FP-26-M6</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4