



Metric table

Dimensions in: millimeters - inches

d ₁	1 2			d ₃	d ₄	h ₁	h ₂	t			
	VB-FP	VB-FP-H									
20 0.79	M 6	-	-	13 0.51	7.5 0.30	15 0.59	7 0.28	11 0.43			
30 1.18	M 5	M 6	M 8	17 0.67	9 0.35	24 0.94	11 0.43	15 0.59			
40 1.57	-	-	-	M 6	M 8	M 10	21 0.83	11 0.43	28 1.10	13 0.51	18 0.71
50 1.97	-	-	-	M 8	M 10	M 12	24 0.94	13 0.51	32 1.26	15 0.59	18 0.71
60 2.36	-	-	-	M 12	-	-	28 1.10	13 0.51	35 1.38	15 0.59	25 0.98
60 2.36	-	-	-	M 16	-	-	28 1.10	17 0.67	35 1.38	15 0.59	25 0.98
70 2.76	-	-	-	M 16	-	-	32 1.26	17 0.67	42 1.65	21 0.83	25 0.98

Specification

- Six-lobed knob
Phenolic plastic
- Temperature resistant up to 300 °F (150 °C)
- Black, shiny finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

On request

- For certain minimum quantities, stainless steel inserts

Information

VB-FP and VB-FP-H six-lobed knobs offer a wide range of clamping.

see also...

- *Six-Lobed Knobs VB (with Blind Tapped Insert)* → page 590
- *Six-Lobed Knobs VP (Solid Type, with Steel Threaded Stud)* → page 592
- *Six-Lobed Knobs VP-H (Hollow Type, with Steel Threaded Stud)* → page 592

How to order (Solid type) 1 2 VB-FP-20-M6	1	Handle diameter d ₁
	2	Thread d ₂
How to order (Hollow type) 1 2 VB-FP-H-40-M8	1	Handle diameter d ₁
	2	Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4