



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	d ₃	h ₁	h ₂	t min.
50 1.97	M 10	23 0.91	30 1.18	10 0.39	16 0.63
50 1.97	M 12	23 0.91	30 1.18	10 0.39	18 0.71

Specification

- Nylon plastic
 - Temperature resistant up to 230 °F (110 °C)
 - Black, textured finish
- Tapped insert
Brass, molded-in
- *Plastic Characteristics* → page QVX
- RoHS compliant

Information

Used in a variety of light duty applications, these VEG textured nylon plastic hand knobs have a comfortable grip.

see also...

- *Ergonomic Hand Knobs VEGS (with Steel Threaded Stud)* → page QVX

How to order ¹ ² VEG-50-M12	1 Handle diameter d ₁
	2 Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

