



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	<sup>3</sup> Length l	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>
50 1.97	M 8	15 0.59	23 0.91	30 1.18	10 0.39
50 1.97	M 10	20 0.79	23 0.91	30 1.18	10 0.39

**Specification**

- Hand knob  
Nylon plastic  
- Temperature resistant up to 230 °F (110 °C)  
- Black, textured finish
- Threaded stud  
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- RoHS compliant

**Information**

VEGS ergonomic hand knobs with threaded stud expand the range of clamping options. These textured knobs are used in a variety of light duty applications and have a comfortable grip.

see also...

- *Ergonomic Hand Knobs VEG (with Brass Tapped Insert)* → [www.jwwinco.com](http://www.jwwinco.com)

<p>How to order</p> <p><sup>1</sup> <sup>2</sup> <sup>3</sup></p> <p><b>VEGS-50-M8-15</b></p>	<b>1</b> Handle diameter d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub>
	<b>3</b> Length l

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4