



Inch table

1		2				Dimensions in: inches - millimeters		
d ₁	d ₂ Thread					d ₃	t	h
1.50 38.1	1/4 x 20	5/16 x 18	3/8 x 16	7/16 x 14	1/2 x 13	0.63 16.0	0.75 19.1	1.44 36.6

Specification

- Knob
Plastic
Polypropylene
 - Temperature resistant up to 250 °F (121 °C)
 - Black, matte finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

Information

WD 595 polypropylene plastic ball knobs are a more shatter and shock resistant option than their phenolic counterpart. Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Ball Knobs DIN 319 (Metric)* → page 55

On request

- For certain minimum quantities:
 - Metric sizes
 - Inserts in other materials
 - Threaded metal studs in brass, zinc plated steel or stainless steel
 - Custom colors and other modifications

How to order	1	Ball diameter d ₁
	2	Thread d ₂
WD 595-1.50-5/16X18		

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4