Fixed Clamping Levers

Plastic, Threaded Stud Type, with Steel Components

JW WINCO® A Ganter Company





Inch

Inch table

Dimensions in: inches / millimeters

1 l_1	2 d_1	3 l_2				d_3	d_4	h_1	h_2	h_3
1.77 45	10 x 32	0.79 20	1.26 32	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35
1.77 45	10 x 24	0.79 20	1.26 32	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35
1.77 45	1/4 x 20	0.79 20	1.26 32	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35
2.48 63	1/4 x 20	0.98 25	-	-	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45
2.48 63	5/16 x 18	0.79 20	1.26 32	1.57 40	2.48 63	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45
2.48 63	3/8 x 16	0.79 20	1.26 32	2.48 63	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45
3.07 78	3/8 x 16	0.79 20	1.26 32	1.57 40	2.48 63	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55
3.62 92	3/8 x 16	1.26 32	2.48 63	-	-	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65
3.62 92	1/2 x 13	1.26 32	1.57 40	2.48 63	-	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65

Specification

4

Lever body

Plastic, Nylon thermoplastic

- Glass fiber reinforced
- With molded-in stainless steel inlay
- Operating temperature up to 230 °F (110 °C)
- Color
  - Black, RAL 9005, textured finish ● **SW**
  - Orange, RAL 2004, textured finish ● **OS**
  - Gray, RAL 7040, matte finish ● **GR**

Threaded stud / Retaining screw

- Steel, blackened finish
- Not removable, loctited
- Property class 5.8

RoHS

On request

- With all stainless steel components
- Special inch and metric bores or threads

Fixed clamping levers WN 400 are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.
The solid steel tapped insert allows the operator the ability to apply additional torque where needed to the item being clamped or fastened.

see also...	Page
WN 400 Fixed Clamping Levers (Nylon Plastic, with Steel Insert)	QVX

Technical Information

Strength Values of Screws	QVX
Plastic Characteristics	QVX

How to order

1 2 3 4

WN 400-45-10X24-20-SW

1	**Lever length l_1**
2	**Thread d_1**
3	**Thread length l_2**
4	**Color**

⚠ **WARNING**: Cancer and Reproductive Harm — www.P65Warnings.ca.gov