



- 3 Identification no.
- 1

With 2 socket cap screws
- 2

With 2 adjustable levers
- 3

With 1 adjustable lever and 1 socket cap screw

Inch table

1		2		Dimensions in: inches - millimeters		
d ₁	s ₁	d ₂	s ₂	k	Length l	m
Bore	Square	Bore	Square	Clamping length		
B 3/8	V 5/16	B 3/8	V 5/16	1.13 28.7	3 76.2	1 25.4
B 1/2	V 7/16	B 1/2	V 7/16	1.13 28.7	3 76.2	1 25.4
B 5/8	V 1/2	B 5/8	V 1/2	1.13 28.7	3 76.2	1 25.4

Specification

- Body
 - Nylon plastic
 - Glass filled
 - Black, matte finish
 - Temperature resistant up to 230 °F (110 °C)
- Socket cap screws DIN 912
 - Stainless steel AISI 304
- Hex nuts
 - Stainless steel AISI 316
- Adjustable lever
 - Glass fiber reinforced thermoplastic
 - Black
 - Insert / screw
 - Stainless steel AISI 303
 - Spring
 - Stainless steel AISI 301
- *Stainless Steel Characteristics → page 2143*
- *RoHS compliant*

Information

WN 600 two-way connector clamps are a very economical choice for your next design.

Two-way connector clamps provide a simple, one-piece solution for applications that require height and width adjustments. One common connection piece (the two-way connector clamp) is used for mounting both a vertical and a horizontal rod through the two-way connector clamp holes (universal square and round), and they are secured via the socket cap screws.

Typically used on conveyors, conveying systems and various types of equipment in the packaging, pharmaceutical, automation and material handling industries.

see also...

- *Two-Way Connector Clamps GN 131 (Aluminum / Stainless Steel) → page 1770*

How to order		1	Bore d ₁
		2	Bore d ₂
		3	Identification no.
WN 600-B3/8-B3/8-1			