



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread			d ₃	d ₄	h ₁	h ₂	t	
22 0.87	M 4	M 5	M 6	M 8	15 0.59	9 0.35	14 0.55	6 0.24	11 0.43
24 0.94	M 4	M 5	M 6	M 8	15 0.59	9 0.35	14 0.55	6 0.24	11 0.43
26 1.02	M 4	M 5	M 6	M 8	16 0.63	9 0.35	15 0.59	6 0.24	11 0.43

Specification

- Nylon plastic
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Tapped insert
Brass, molded-in
- *Plastic Characteristics* → page QVX
- RoHS compliant

Information

More shock proof than their phenolic counterpart, these ZB-FP knurled nuts provide excellent slip-free clamping and fastening.

see also...

- *Knurled Nuts ZB (with Brass Tapped or Plain Blind Bore Insert)* → page QVX

How to order ¹ ² ZB-FP-24-M5	1 Handle diameter d ₁
	2 Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

