



Metric



**4 Sensitivity**

30 Angular minutes, bubble moves by 2 mm

**5 Type**

- A With smooth reference surface
- B With threaded stud for mounting

Metric table

**2**

Dimensions in: millimeters / inches

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>
14 0.55	10 0.39	M 4	9.5 0.37	7.7 0.30	5 0.20
20 0.79	14 0.55	M 5	13 0.51	13 0.51	6 0.24
30 1.18	21 0.83	M 6	15 0.59	15 0.59	7.5 0.30

**Specification**

**Housing**

- Aluminum
- Anodized finish, natural color ● ALN
- Anodized finish, black ● ALS

**Spirit level element**

- Glass plastic body
- Filling
- Colorless-transparent **K**

**Casting compound**

Mineral-based

RoHS

**On request**

- Green transparent filling
- Other sensitivities
- Housing in brass or stainless steel

Bull's eye spirit levels GN 2279 are used to check the horizontal position of jigs, machines, devices, appliances and instruments. Type A is suggested if the spirit level is to be used as a tool, e.g. at different measuring points.

The spirit levels are aligned in relation to the reference surface so that the bubble is centrally located inside the marking ring when the horizontal position of the contact surface is achieved.

see also...

	Page
GN 2280 Bull's Eye Spirit Levels (Adjustable)	QVX
GN 2277 Bull's Eye Spirit Levels (with Mounting Flange)	QVX
GN 2278 Bull's Eye Spirit Levels (for Insertion into Bore Holes)	QVX
GN 2276 Cross Spirit Levels (with Mounting Holes)	QVX

**Technical Information**

General Information on Bull's Eye, Screw-On and Cross Spirit Levels	QVX
---	-----

How to order

<b>1</b> Color
<b>2</b> Outside diameter d <sub>1</sub>
<b>3</b> Filling
<b>4</b> Sensitivity
<b>5</b> Type

**GN 2279-ALS-20-K-30-A**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

