



SS Stainless Steel

4 Type

- A** With lanyard ring only
- H** With retaining cable
- K** With ball chain

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread	Length l					d ₃	h ₁	h ₂	h ₃	r ≈	s	t min.
		20	30	40	50	60							
40 1.57	M 8	0.79	1.18	1.57	-	14 0.55	24 0.94	12 0.47	3.2 0.13	22.3 0.88	2.8 0.11	15 0.59	
50 1.97	M 10	0.79	1.18	1.57	-	18 0.71	30 1.18	17 0.67	3.9 0.15	29.6 1.17	3.2 0.13	18 0.71	
60 2.36	M 12	0.79	1.18	1.57	1.97	20 0.79	38 1.50	20 0.79	3.9 0.15	30.7 1.21	3.2 0.13	22 0.87	

Specification

- Star knob
Stainless steel AISI 316L
- Hub welded
- Matte shot-blasted finish
- Tapped insert / threaded stud
Stainless steel AISI 304
- Lanyard ring GN 111.6
Stainless steel AISI 301
- Ball chain GN 111.5 (Type K)
Stainless steel AISI 301
- Retaining cable GN 111.2 (Type H)
Stainless steel
Coated with clear plastic
- RoHS compliant

Information

GN 5334.13 star knobs with loss protection can be attached to a base element with the help of a ball chain or a retaining cable.

The star knobs are supplied ready assembled (with lanyard ring, with lanyard ring and retaining cable, or with lanyard ring and ball chain).

see also...

- Ball Chains GN 111.5 (Stainless Steel)
- Retaining Cables GN 111.2 (Stainless Steel)
- Spiral Retaining Cables GN 111.4
- Lanyard Rings GN 111.6 (Stainless Steel)
- More Star Knobs with Loss Protections GN 111.7

On request

- Ball chains / retaining cables with other lengths
- With spiral retaining cable GN 111.4
- Other GN / DIN series with loss protection

How to order (Tapped insert)	1 Handle diameter d ₁
GN 5334.13-40-M8-H	2 Thread d ₂
	4 Type

How to order (Threaded stud)	1 Handle diameter d ₁
GN 5334.13-60-M12-40-A	2 Thread d ₂
	3 Length l
	4 Type