



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	³ Length l			d ₄	h ₁	h ₂
40 1.57	M 8	16 0.63	20 0.79	25 0.98	18 0.71	30.5 1.20	15 0.59
50 1.97	M 10	20 0.79	25 0.98	30 1.18	21 0.83	34 1.34	17 0.67
60 2.36	M 12	25 0.98	30 1.18	40 1.57	25 0.98	39 1.54	18 0.71

Specification

- Stainless steel AISI 303
Matte shot-blasted finish
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Other threaded stud lengths

Information

GN 5335 star knobs are specially designed for the food processing machinery industry. The smooth and enclosed areas as well as the large corner radii comply with the requirements of hygiene standards.

see also...

- *Star Knobs GN 5334 (Stainless Steel)* → page 617
- *Star Knobs GN 5334.4 (Stainless Steel)* → page 617
- *Wing Screws GN 433 (Stainless Steel)* → page 678
- *Wing Screws GN 835 (Stainless Steel)* → page 677

How to order

¹ ² ³
GN 5335-40-M8-20

¹	Handle diameter d ₁
²	Thread d ₂
³	Length l