



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$	$d_3$	$d_4$	$h$	$k$
40 1.57	M 8	12 0.47	25 0.98	10 0.39	8.5 0.33
40 1.57	M 10	13 0.51	25 0.98	10 0.39	8.5 0.33

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to  
212 °F (100 °C)  
- Black, matte finish



- Tapped insert  
Brass
- Plastic Characteristics → page QVX
- RoHS compliant

**On request**

- Additional thread sizes

**Information**

EN 567 lobed thumb nuts can be used to lock and secure by utilizing two thumb nuts on a threaded shaft. They also require minimal space due to their thin profile.

The ergonomic shape makes them easy to grip during use.

see also...

- Flat Knurled Nuts DIN 467 → page QVX

How to order	
<sup>1</sup> $d_1$	1 Handle diameter $d_1$
<sup>2</sup> $d_2$	2 Thread $d_2$
<sup>3</sup> Color	3 Color

**EN 567-40-M8-SW**