



Metric



elesa
Original design BT.S-p-SST

SS Stainless Steel

Metric table

Dimensions in: millimeters / inches

| d₁ | d₂ | Length l | | | | | d₃ | h | k |
|----------------------|----------------------|-----------------|------------|------------|------------|------------|----------------------|--------------|-------------|
| 12 0.47 | M 3 | 6 0.24 | 10 0.39 | 16 0.63 | - | - | 9.5 0.37 | 11.5 0.45 | 7.5 0.30 |
| 16 0.63 | M 3 | 6 0.24 | 10 0.39 | 16 0.63 | - | - | 11 0.43 | 13 0.51 | 8 0.31 |
| 16 0.63 | M 4 | 6 0.24 | 10 0.39 | 16 0.63 | - | - | 11 0.43 | 13 0.51 | 8 0.31 |
| 16 0.63 | M 5 | 10 0.39 | 16 0.63 | 25 0.98 | - | - | 11 0.43 | 13 0.51 | 8 0.31 |
| 20 0.79 | M 5 | 10 0.39 | 16 0.63 | 25 0.98 | - | - | 12 0.47 | 16 0.63 | 10 0.39 |
| 20 0.79 | M 6 | 10 0.39 | 16 0.63 | 20 0.79 | 25 0.98 | 30 1.18 | 12 0.47 | 16 0.63 | 10 0.39 |
| 25 0.98 | M 6 | 16 0.63 | 20 0.79 | 25 0.98 | 30 1.18 | - | 16 0.63 | 19 0.75 | 11 0.43 |
| 32 1.26 | M 8 | 16 0.63 | 20 0.79 | 30 1.18 | - | - | 17 0.67 | 22 0.87 | 13 0.51 |

Specification

Knob

Plastic, Polyamide (PA)

- Reinforced
- Operating temperature
-22 °F to 266 °F (-30 °C to +130 °C)
- Black, matte finish

Threaded stud

Stainless steel AISI 303

RoHS

Knurled screws EN 591.5 are used for quick, tool-free mounting or adjusting of fixtures and devices.

With the stainless steel threaded studs, they are also suitable for applications that place increased demands on the corrosion resistance of the components used.

see also...

| | Page |
|--|------|
| EN 591 Knurled Screws (Steel Threaded Stud) | QVX |
| GN 421 Hollow Knurled Screws | QVX |

Technical Information

| | |
|---------------------------------|-----|
| Plastic Characteristics | QVX |
| Stainless Steel Characteristics | QVX |

How to order

EN 591.5-20-M5-16

- | | |
|----------|--------------------------------------|
| 1 | Handle diameter d₁ |
| 2 | Thread d₂ |
| 3 | Length l |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

