



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<sup>2</sup> d <sub>1</sub>	<sup>3</sup> d <sub>2</sub>	<sup>4</sup> Length l					d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>
40 1.57	M 8	20 0.79	25 0.98	30 1.18	40 1.57	-	14 0.55	25 0.98	12 0.47
50 1.97	M 10	20 0.79	25 0.98	30 1.18	45 1.77	55 2.17	18 0.71	32 1.26	15 0.59
63 2.48	M 12	30 1.18	40 1.57	50 1.97	-	-	20 0.79	40 1.57	19 0.75

**Specification**

<sup>1</sup>

- Star knob  
Stainless steel precision casting  
AISI 316  
Polished finish
- Threaded stud  
Stainless steel A4
- The threaded stud is screwed in and secured by a cross-dowel pin (Stainless steel A4)
- Stainless Steel Characteristics → page QVX
- RoHS compliant

A4P

**Information**

GN 6336.5 star knobs satisfy the dimensions of the DIN 6336 type L but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygienic requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

- Star Knobs GN 6336.4 / GN 6336.5 (Plastic) → page QVX
- Star Knobs GN 6336.4 / GN 6336.5 (Cast Iron / Stainless Steel / Aluminum) → page QVX
- Star Knobs GN 5334 / GN 5334.4 (Stainless Steel) → page QVX

How to order

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup>  
**GN 6336.5-A4P-63-M12-40**

<sup>1</sup>	Material
<sup>2</sup>	Handle diameter d <sub>1</sub>
<sup>3</sup>	Thread d <sub>2</sub>
<sup>4</sup>	Length l

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

