



- 3 Type**
- J Without symbol
 - L With fill symbol
 - M** With drain symbol
- 4 Identification no.**
- 1 Without vent hole
 - 2 With vent hole

Metric table

1 s	2 d ₁ Pipe thread	l ₁	l ₂
17 0.67	G 1/4	10 0.39	16 0.63
22 0.87	G 1/4	10 0.39	17 0.67
22 0.87	G 3/8	11 0.43	18 0.71
26 1.02	G 1/2	12 0.47	19 0.75
32 1.26	G 3/4	12 0.47	20 0.79
38 1.50	G 1	13* 0.51	22 0.87

Dimensions in: millimeters - inches

*l₁ = 18 mm for item TO-38-G1-L-2 **Only available with vent hole

Specification

- Body
Nylon plastic
- Black finish
- Temperature resistant up to 158 °F (70 °C)
- Plastic Characteristics → page QVX

Information

TO fluid fill / drain plugs are provided with a two way vent hole allowing the tank to breathe.

see also...

- Fluid Plugs TAO / TCA (wth or without Fluid Symbol) → page QVX

How to order	1 Width s
1 2 3 4 TO-17-G1/4-J-1	2 Pipe thread d ₁
	3 Type
	4 Identification no.