



Metric



Metric table

Dimensions in: millimeters / inches

1 b	2 d	3 l ₁	h ₁	h ₂	l ₂	l ₃
25 0.98	B 6.5	110 4.33	44 1.73	24 0.94	130 5.12	88 3.46

Specification

Handle

- Nylon plastic
- Black, RAL 9005, matte finish
- Glass fiber reinforced
- Operating temperature up to 230 °F (110 °C)

Cover strip

Orange, RAL 2004, matte finish

Mounting holes

Through holes for inch or metric hex cap screws or low socket cap screws

RoHS

On request

- Additional colors
- Various metric and inch size fasteners and kit packaging

Pull handle MFA is a „safety handle“ with a 15° angle, and is used where a reach-through of the fingers is not permitted.

Technical Information

Plastic Characteristics

Page

QVX

How to order

MFA-25-B6.5-110

- 1** Handle width b
- 2** Bore d
- 3** Length l₁