



Inch



SS Stainless Steel

4 Type

B With through holes

Inch table

Dimensions in: inches / millimeters						
l ₁	l ₂	d ₁	d ₂	m ₁	m ₂	s
1.50 38.1	1.50 38.1	0.157 4	0.201 5.1	1.00 25.4	1.00 25.4	0.0787 2
2.00 50.8	2.00 50.8	0.236 6	0.201 5.1	1.25 31.75	1.25 31.75	0.0787 2

Specification

Hinge leafs

- Steel, zinc plated, blue passivated finish
- Stainless steel AISI 304

ST
NI

Hinge pin

Stainless steel AISI 304
Riveted

RoHS

Sheet metal hinges WN 136 are a low-cost option for light load applications. The stainless steel versions are particularly suited for applications in highly aggressive conditions.

see also...	Page
GN 1362 Sheet Metal Hinges (Stainless Steel, Weldable)	QVX
GN 1364 Sheet Metal Hinges (Stainless Steel)	QVX
GN 1366 Hinges (Steel Profile, Weldable)	QVX

Technical Information

List of Hinge Types	QVX
Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order		1	Material
2	Width l ₁	2	Width l ₁
3	Length l ₂	3	Length l ₂
4	Type	4	Type
WN 136-NI-2.00-2.00-B			