

- 3 Type**
A Without handle
D With revolving steel handle
- 4 Coding**
ZI Engage by pulling
DR Engage by pushing

Metric table

Dimensions in: millimeters - *inches*

1 d₁	2 d₂ H7 Bore with keyway GN 000.4 GN 000.5		d₃		d₄ max.	l₁		l₂	l₃		l₄	r	w min.	Ø Handle	Coupling Size GN 000.4 GN 000.5
	GN 000.4	GN 000.5	GN 000.4	GN 000.5		GN 000.4	GN 000.5		GN 000.4	GN 000.5					
125 4.92	K 12	-	28 1.10	29 1.14	17 .67	28.5 1.12	42 1.65	18 .71	5 .20	12 .47	67.5 2.66	54 2.13	4 .16	23 .91	1
140 5.51	K 12	-	28 1.10	29 1.14	17 .67	28.5 1.12	42 1.65	19 .75	5 .20	12 .47	67.5 2.66	61 2.40	4 .16	23 .91	1
140 5.51	K 14	K 16	32 1.26	33 1.30	21 .83	32.5 1.28	48 1.89	19 .75	6 .24	14 .55	67.5 2.66	61 2.40	4 .16	23 .91	2
160 6.30	K 14	K 16	32 1.26	33 1.30	21 .83	32.5 1.28	48 1.89	20 .79	6 .24	14 .55	82.5 3.25	71 2.80	4 .16	26 1.02	2
200 7.87	K 18	K 20	38 1.50	39 1.54	26 1.02	36.5 1.44	50 1.97	24 .94	6 .24	13 .51	82.5 3.25	89 3.50	4 .16	26 1.02	3
250 9.84	K 22	-	45 1.77	46 1.81	30 1.18	47.5 1.87	54 2.13	28 1.10	12 .47	13 .51	92.5 3.64	113 4.45	4 .16	28 1.10	4

Specification

- Handwheels see following page respectively standard sheets
- Coupling elements
- Safety clutch assemblies GN 000.4
- Safety clutch assemblies GN 000.5
- Keyway P9 DIN 6885/2
- ISO-Fundamental tolerances
- RoHS compliant

Information

The use of safety clutch assemblies in handwheels other than specified on this sheet is also possible.

see also...


- More information to Safety Clutch Handwheels
- Countersunk Washers GN 184 (for Axial Fixing)

* Insert the code-no. of the desired handwheels (here in How to order: GN 321).

How to order GN 321.4-140-K-D-DR	1	Handwheel diameter d₁
	2	Bore d₂
	3	Type
	4	Coding

Safety Clutch Handwheels

Overview of types




Solid disk handwheels GN 321

Aluminum
Rim turned and highly polished on all sides

Revolving handles GN 598

Steel
Powder coated
Black, matte textured finish




Solid disk handwheels GN 323

Aluminum
Powder coated
Black, matte textured finish

Revolving handles GN 598

Steel
Powder coated
Black, matte textured finish



Spoked handwheels GN 322

Aluminum
Rim turned and highly polished on all sides

Revolving handles GN 598

Steel
Powder coated
Black, matte textured finish

1.1

1.2

1.3

1.4

2.1

2.2

2.3

2.4

