























Shaft Collars

Types

Application	Set screw shaft collars	Semi-split shaft collars	Split shaft collars
Universally applicable	<p>GN 705 complies with DIN 705</p>  <p>Page 1204</p>	<p>GN 706.2 Standard version</p>  <p>Page 1206</p>	<p>GN 707.2 Standard version</p>  <p>Page 1214</p>
		<p>GN 706.3 Threaded shaft collars</p>  <p>www.jwwinco.com</p>	<p>GN 707.5 Plastic</p>  <p>www.jwwinco.com</p>
		<p>GN 706.4 With adjustable lever</p>  <p>Page 1210</p>	
		<p>GN 704 Quick release shaft collars</p>  <p>Page 1212</p>	
	Sensor attachment		<p>GN 7062.1 - Type A Tapped holes, radial</p>  <p>Page 1207</p>
		<p>GN 7062.1 - Type B Tapped holes, axial</p>  <p>Page 1207</p>	<p>GN 7072.1 - Type B Tapped holes, axial</p>  <p>Page 1215</p>

Application	Semi-split shaft collars <ul style="list-style-type: none"> • Axial assembly • Clamping by reducing the slot height using a socket cap screw • Non-positive / damage-free clamping 	Split shaft collars <ul style="list-style-type: none"> • Axial / radial assembly • Clamping by reducing the slot height using a socket cap screw • Non-positive / damage-free clamping 	
Flange mounting	<p>GN 7062.2 - Type A With two plain holes</p>  <p>Page 1208</p>	<p>GN 7072.2 - Type A With two plain holes</p>  <p>Page 1216</p>	
	<p>GN 7062.2 - Type B With two countersunk holes</p>  <p>Page 1208</p>	<p>GN 7072.2 - Type B With two countersunk holes</p>  <p>Page 1216</p>	
	<p>GN 7062.2 - Type C With two tapped holes</p>  <p>Page 1208</p>	<p>GN 7072.2 - Type C With two tapped holes</p>  <p>Page 1216</p>	
	Damping	<p>GN 7062.3 With damping washer</p>  <p>Page 1209</p>	<p>GN 7072.3 With damping washer</p>  <p>Page 1217</p>
		<p>GN 7062.30 Damping washers</p>  <p>Page 1220</p>	<p>GN 7072.30 Damping washers</p>  <p>Page 1220</p>
	Accessories	 <p>GN 311 Adjustable levers</p> <p>Page 1218</p>	
 <p>GN 7062.10 Stainless steel sensor brackets</p> <p>Page 1219</p>			