


Linear Actuator Connectors

Overview of Types



Series		Material		Cross section		Interfering contours		Slide insert available	Lever available as accessory
		AL	NI	d ₁	s	k Clamping Length	x Flange		
GN 131.1 GN 131.2 Page XYZ		x	x	18	-	25	-	Yes	Yes
GN 132.1 GN 132.2 Page XYZ		x	-	30 40 50 60	-	40 56 65 80	-	Yes	Yes
GN 132.15 GN 132.25 Page XYZ		-	x	30 50	-	40 65	-	Yes	Yes
GN 133.1 GN 133.2 Page XYZ		x	-	18 30 50	-	40 65	-	Yes	Yes
GN 134.1 GN 134.2 GN 135.1 Page XYZ		x	-	30 40 50	30 40 50	50 60 76	-	Yes	Yes
GN 145.1 Page XYZ		x	-	18	-	25	35	Yes	Yes
GN 146.1 GN 146.13 Page XYZ		x	-	30 40 50 60	-	40 56 65 80	52 78 92 110	Yes	Yes
GN 146.15 GN 146.16 Page XYZ		-	x	30 50	-	40 65	52 92	Yes	Yes

Linear Actuator Connectors

Overview of Types

Series		Material		Cross section		Interfering contours		Slide insert	Lever
		AL	NI	d ₁	s	k Clamping Length	x Flange	available	available as accessory
GN 147.1 Page XYZ		x	-	-	30 40 50	50 76	50 76	No	Yes
GN 162.1 Page XYZ		x	x	18	-	40	-	Yes	Yes
GN 163.1 Page XYZ		x	-	30 40 50 60	-	50 70 85 100	-	Yes	No
GN 163.15 Page XYZ		-	x	30 50	-	50 85	-	Yes	Yes
GN 165.1 Page XYZ		x	-	-	30 40 50	58 91	-	No	Yes
GN 273.1 Page XYZ		x	-	18	-	25	-	Yes	Yes
GN 274.1 Page XYZ		x	-	30 40 50	-	40 65	-	Yes	Yes
GN 277.1 Page XYZ		x	-	18	-	25	-	Yes	Yes
GN 278.1 Page XYZ		x	-	30 40 50	-	40 65	-	Yes	Yes
GN 191.1 Page XYZ		x	x	18	-	25	-	Yes	Yes
GN 192.1 Page XYZ		x	-	30 40 50 60	-	40 56 65 80	-	Yes	Yes
GN 192.15 Page XYZ		-	x	30 50	-	37 65	-	Yes	Yes