


Inch table

Dimensions in: inches / millimeters										
d ₁	d ₂			d ₃	h ₁	h ₂	h ₃ ≈	h ₄ Stroke	l ₂	t min.
0.55 14	10 x 32	10 x 24	1/4 x 20	0.39 10	0.98 25	0.18 4.5	1.38 35	0.14 3.5	1.77 45	0.35 9
0.71 18	1/4 x 20	5/16 x 18	-	0.53 13.5	1.22 31	0.26 6.5	1.77 45	0.16 4	2.44 62	0.43 11
0.87 22	5/16 x 18	3/8 x 16	-	0.63 16	1.42 36	0.31 8	2.05 52	0.16 4	2.91 74	0.55 14
0.98 25	3/8 x 16	1/2 x 13	-	0.75 19	1.69 43	0.43 11	2.48 63	0.16 4	3.50 89	0.67 17
1.18 30	1/2 x 13	5/8 x 11	-	0.91 23	1.99 50.5	0.47 12	2.99 76	0.20 5	4.25 108	0.87 22

Metric table

Dimensions in: millimeters / inches										
d ₁	d ₂			d ₃	h ₁	h ₂	h ₃ ≈	h ₄ Stroke	l ₂	t min.
14 0.55	M 5	M 6		10 0.39	25 0.98	4.5 0.18	35 1.38	3.5 0.14	45 1.77	9 0.35
18 0.71	M 6	M 8		13.5 0.53	31 1.22	6.5 0.26	45 1.77	4 0.16	62 2.44	11 0.43
22 0.87	M 8	M 10		16 0.63	36 1.42	8 0.31	52 2.05	4 0.16	74 2.91	14 0.55
25 0.98	M 10	M 12		19 0.75	43 1.69	11 0.43	63 2.48	4 0.16	89 3.50	17 0.67
30 1.18	M 12	M 16		23 0.91	50.5 1.99	12 0.47	76 2.99	5 0.20	108 4.25	22 0.87

Specification

Lever body

- Zinc die-cast
- Powder coated
- Black, RAL 9005, textured finish
- Orange, RAL 2004, textured finish



Tapped insert / Retaining screw

Steel, blackened finish

RoHS

On request

- Special colors and threads

Adjustable levers GN 101 have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged. Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

	Page
GN 101.1 Adjustable Levers (Stainless Steel Insert)	QVX
GN 300 Adjustable Levers (Steel Insert, Blackened Finish)	QVX
GN 302 Straight Adjustable Levers (Steel Insert , Blackened Finish)	QVX
GN 300.2 Adjustable Levers (Steel Insert, Zinc Plated)	QVX

How to order (Inch)

GN 101-14-10X32-SW

- 1 Diameter d₁
- 2 Thread d₂
- 3 Color

How to order (Metric)

GN 101-25-M12-OS

- 1 Diameter d₁
- 2 Thread d₂
- 3 Color