



**Metric table**

Dimensions in: millimeters - inches

No.	d <sub>1</sub> Handwheel Ø GN 321 GN 322 GN 323	d <sub>2</sub> H7 Bore with keyway		d <sub>3</sub>	d <sub>4</sub> max. see page XYZ	d <sub>5</sub> Minimum Ø of wheel hub	d <sub>6</sub> -0.03 Location hole of wheel hub d <sub>6</sub> H7	l <sub>1</sub>	l <sub>2</sub> ±0.1 Length of wheel hub	l <sub>3</sub>	t	w min. see page XYZ
1	125 4.92	K 12	-	28 1.10	17 0.67	29 1.14	25 0.98	28.5 1.12	18 0.71	5 0.20	26 1.02	4 0.16
1	140 5.51	K 12	-	28 1.10	17 0.67	29 1.14	25 0.98	28.5 1.12	19 0.75	5 0.20	26 1.02	4 0.16
2	140 5.51	K 14	K 16	32 1.26	21 0.83	33 1.30	29 1.14	32.5 1.28	19 0.75	6 0.24	30 1.18	4 0.16
2	160 6.30	K 14	K 16	32 1.26	21 0.83	33 1.30	29 1.14	32.5 1.28	20 0.79	6 0.24	30 1.18	4 0.16
3	200 7.87	K 18	K 20	38 1.50	26 1.02	39 1.54	35 1.38	36.5 1.44	24 0.94	6 0.24	36 1.42	4 0.16
4	250 9.84	K 22	-	45 1.77	30 1.18	46 1.81	41 1.61	47.5 1.87	28 1.10	12 0.47	42 1.65	4 0.16

**Specification**

- Steel, nitrided
- Bearing surfaces ground resp. PTFE coated
- RoHS compliant

**Information**

The PTFE coated bearing surfaces of the GN 000.4 safety clutch assemblies guarantee minimal friction and best wear resistance.

An oil hole is provided which is connected to a pressure oiler in the wheel hub when the safety clutch handwheel is completely assembled.

The length of the wheel hub l<sub>2</sub> can be set to the corresponding value given in the table by turning the clamping nut.

see also...

- [More Information on Safety Clutch Handwheels](#)

<p>How to order</p> <p><b>GN 000.4-2-K14</b></p>	1 No.
	2 Bore with keyway d <sub>2</sub>