


Metric



Type

- DK** With triangular spindle
- VK7** With square spindle
- VK8** With square spindle
- SCH** With slot
- VDE** With double bit
- SK10** With hex



Metric table



Dimensions in: millimeters - inches

Latch distance A												d	h
4	8	13	16	20	24	28	32	36	40	45		28	4
0.16	0.31	0.51	0.63	0.79	0.94	1.10	1.26	1.42	1.57	1.77		1.10	0.16
6	10	14	18	22	26	30	34	38	42	50		28	4
0.24	0.39	0.55	0.71	0.87	1.02	1.18	1.34	1.50	1.65	1.97		1.10	0.16

Specification



- Cam latch housing
Zinc die-cast
- Housing collar
 - Chrome plated finish —
 - Powder coated
Black, RAL 9005, textured finish ● **SW**
- Latch arm / assembly hardware
Steel, zinc plated, blue passivated finish
- **RoHS compliant**

Accessory

- Socket keys GN 119.2 → page 1310
- Protective caps GN 120
→ www.jwwinco.com
- Opening handles GN 120.1
→ www.jwwinco.com
- Protective guide plates GN 120.2
→ www.jwwinco.com

On request

- Other operations

Information

GN 115 cam latches close via a turning operation limited to 90° (quarter of a turn), which moves the latch arm behind the door frame. The beveled edges of the latch arm create a smooth latching of the door.

The 22 different off-set latch arm options allow for “Latch distance A” to be set between 4 mm and 50 mm.

Product comes supplied with a loosely enclosed latch arm.

The socket key latches the latch arm and provides security from accidentally opening but does not lock the arm in place.

A socket key is not included.

see also...

- *Construction and Assembly Instructions* → page 1261
- *List of Cam Latch / Cam Lock Types* → page 1256
- *Cam Latches GN 115 (Zinc Die-Cast, with Operating Elements)* → page 1260
- *Cam Latches GN 115 (Stainless Steel, Operation with Socket Key)* → page 1267

How to order (Chrome plated housing collar) 	1	Type
	2	Latch distance A
GN 115-VK8-20		

How to order (Powder coated housing collar) 	1	Type
	2	Latch distance A
	3	Finish (Housing collar)
GN 115-SCH-32-SW		