



Specification



- Lever body
Zinc die-cast
- Powder coated
Black, RAL 9005, textured finish **SW**
Orange, RAL 2004, textured finish **OS**
- Threader stud / retaining screw
Steel
- Blackened finish
- Tensile strength class 5.8
- RoHS compliant

Information

GN 101 adjustable levers have proven to be ideal whenever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.
Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

On request

- Special colors, stud lengths, and threads

How to order (Inch)	1 Diameter d ₁
1 2 3 4	2 Thread d ₂
GN 101-14-10X32-10-SW	3 Thread length l ₁
	4 Color

How to order (Metric)	1 Diameter d ₁
1 2 3 4	2 Thread d ₂
GN 101-22-M10-40-OS	3 Thread length l ₁
	4 Color

Inch table

Dimensions in: inches - millimeters

1 d ₁	2 d ₂ Thread	3 l ₁									d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	l ₂
.55 14	10 x 32	.39 10	.47 12	.63 16	.79 20	.98 25	1.26 32	-	-	-	.39 10	.98 25	.18 4.5	1.38 35	.14 3.5	1.77 45
.55 14	10 x 24	.47 12	.63 16	.79 20	.98 25	1.26 32	-	-	-	-	.39 10	.98 25	.18 4.5	1.38 35	.14 3.5	1.77 45
.55 14	1/4 x 20	.39 10	.47 12	.63 16	.79 20	.98 25	1.26 32	1.57 40	1.77 45	-	.39 10	.98 25	.18 4.5	1.38 35	.14 3.5	1.77 45
.71 18	1/4 x 20	.47 12	.63 16	.79 20	.98 25	-	-	-	-	-	.53 13.5	1.22 31	.26 6.5	1.77 45	.16 4	2.44 62
.71 18	5/16 x 18	.47 12	.63 16	.79 20	.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	.53 13.5	1.22 31	.26 6.5	1.77 45	.16 4	2.44 62
.71 18	3/8 x 16	.63 16	.79 20	.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	.53 13.5	1.22 31	.26 6.5	1.77 45	.16 4	2.44 62
.87 22	3/8 x 16	.63 16	.79 20	.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	.63 16	1.42 36	.31 8	2.05 52	.16 4	2.91 74
.87 22	1/2 x 13	.63 16	.79 20	.98 25	1.26 32	1.57 40	1.77 45	1.97 50	-	-	.63 16	1.42 36	.31 8	2.05 52	.16 4	2.91 74
.98 25	3/8 x 16	.63 16	.79 20	.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	.75 19	1.69 43	.43 11	2.48 63	.16 4	3.50 89
.98 25	1/2 x 13	.63 16	.79 20	.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	.75 19	1.69 43	.43 11	2.48 63	.16 4	3.50 89
1.18 30	1/2 x 13	.98 25	1.26 32	1.57 40	1.97 50	2.17 55	2.48 63	-	-	-	.91 23	1.99 50.5	.47 12	2.99 76	.20 5	4.25 108
1.18 30	5/8 x 11	1.26 32	1.57 40	1.97 50	2.17 55	2.48 63	-	-	-	-	.91 23	1.99 50.5	.47 12	2.99 76	.20 5	4.25 108

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread	3 l ₁									d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	l ₂
14 .55	M 5	M 6	12 .47	16 .63	20 .79	25 .98	32 1.26	40 1.57	50 1.97	10 .39	25 .98	4.5 .18	35 1.38	3.5 .14	45 1.77	
18 .71	M 6	M 8	16 .63	20 .79	25 .98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 .53	31 1.22	6.5 .26	45 1.77	4 .16	62 2.44	
22 .87	M 10	-	20 .79	25 .98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 .63	36 1.42	8 .31	52 2.05	4 .16	74 2.91	
25 .98	M 12	-	25 .98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	19 .75	43 1.69	11 .43	63 2.48	4 .16	89 3.50	
30 1.18	M 16	-	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	23 .91	50.5 1.99	12 .47	76 2.99	5 .20	108 4.25	

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

