



SS Stainless Steel

1 Type

- Operation with
- SG** star knob
- DK** triangular spindle (DK7)
- VK7** square spindle A/F7
- VK8** square spindle A/F8
- VDE** double bit

Metric table

2

Dimensions in: millimeters - inches

| Clamping range A1 - A9 (Door + frame thickness) | | | | | | | | |
|--|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| A 1 (l = 35) (l = 1.38) | A 2 (l = 40) (l = 1.57) | A 3 (l = 45) (l = 1.77) | A 4 (l = 50) (l = 1.97) | A 5 (l = 55) (l = 2.17) | A 6 (l = 60) (l = 2.36) | A 7 (l = 65) (l = 2.56) | A 8 (l = 70) (l = 2.76) | A 9 (l = 75) (l = 2.95) |
| 17 - 25 0.67 - 0.98 | 22 - 30 0.87 - 1.18 | 27 - 35 1.06 - 1.38 | 32 - 40 1.26 - 1.57 | 37 - 45 1.46 - 1.77 | 42 - 50 1.65 - 1.97 | 47 - 55 1.85 - 2.17 | 52 - 60 2.05 - 2.36 | 57 - 65 2.24 - 2.56 |

Specification

3

- Cam latch housing / operating bolt
Stainless steel AISI 303 **NI**
- Cam latch arm
Stainless steel AISI 304
- Star knob GN 5334
Stainless steel AISI 304
- Protection class IP 65
- RoHS compliant

Information

GN 119 stainless steel door cam latches have a large draw-in range of up to 10 mm. Securing the cam latch is achieved by turning the knob clockwise.

The operating spindle includes an o-ring, which prevents the penetration of water.

see also...

- *Construction and Assembly Instructions*
- *List of Cam Latch Types*
- *Door Cam Latches GN 119*

Accessory

- Socket keys GN 119.2
- Protective caps GN 120
- Opening handles GN 120.1

| | |
|------------------------|---------------------------|
| How to order | 1 Type |
| GN 119-SG-A3-NI | 2 Clamping range A |
| | 3 Material |