



**3 Type**

- A Mounting with countersunk screw
- B Mounting with adhesive pad

**Metric table**

Dimensions in: millimeters - inches

1	2							
h	b <sub>1</sub>	b <sub>2</sub>	d <sub>1</sub> Thread	d <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	m <sub>1</sub>	m <sub>2</sub> ±2
60 2.36	4 0.16	4.6 0.18	M 4	3 0.12	20 0.79	10 0.39	40 1.57	35 1.38

**Specification**

- Guide plate  
Plastic  
Technopolymer (Polyamide PA)  
Black, matte finish ● SW
- Adhesive pad (only Type B)  
Scotch-Mount™ 4026  
Double-sided, with polyurethane foam backing
- [Plastic Characteristics](#) → page QVX
- [RoHS compliant](#)



**Information**

GN 120.2 protective guide plates are used in connection with cam door latches, using the principle of friction. They prevent the latch arm from causing abrasion, for example, to the corrosion protection layers on a door frame. They additionally prevent unintended opening, as the latch arms lock into a small recess in their closed position.

If the d<sub>2</sub> positioning tabs are not required they can easily be removed with side cutting pliers.

GN 120.2 protective guide plates are suitable for the following cam latches / cam locks:

- GN 115 cam latches / cam locks → starting from page QVX
- GN 115.7 cam latches (with cabinet "U" handle) → page QVX
- GN 115.9 safety cam latches → page QVX
- GN 115.10 cam latches (with gripping tray) → starting from page QVX
- GN 515 cam latches / cam locks (with extended housing) → page QVX

**How to order**

**GN 120.2-60-4-A-SW**

- 1 Height h
- 2 Width b<sub>1</sub>
- 3 Type
- 4 Color