



ELESA original design CFP. / CFQ.

3 Type

- SH** 2x2 bores for countersunk screws
- CH** 2x2 bores for socket cap screws
- EH** 2x2 bores for hexagon head screws

Metric table

Dimensions in: millimeters - inches

1	2												
l_1	l_2	l_3	d_1	d_2	h_1	h_2	h_3	m_1	m_2	t_1	t_2	Max. holding torque M_{H_i} in Nm	
45 1.77	50 1.97	21.5 0.85	4.5 0.18	8 0.31	14 0.55	8 0.31	7 0.28	25 0.98	32 1.26	4.5 0.18	4.5 0.18	1.1	

Specification

- Body
Plastic
Technopolymer (Polyacetal POM)
- Glass fiber reinforced
- Black, matte finish
- Temperature resistant up to 176 °F (80 °C)
- Pin
Plastic
Technopolymer (Polyacetal POM)
- RoHS compliant

Information

EN 122.1 hinges with indexing positions keep the door in the three specified positions without additional mechanism.

EN 122.2 hinges without indexing positions are dimensionally the same as EN 122.1 hinges.

The covers not only prevent the entering of dirt to the screw areas, but also give an appealing appearance to the hinges.

see also...

- [List of Hinge Types](#)

How to order (With indexing positions) EN 122.1-45-50-SH	1 Width l_1
	2 Length l_2
	3 Type
How to order (Without indexing positions) EN 122.2-45-50-SH	1 Width l_1
	2 Length l_2
	3 Type